

Unit: AE-PLC-MR2. Rotary Table Workstation 2

INTRODUCTION

Since the 1950s, the computer integration in the manufacturing systems has been a complete revolution, increasing productivity and quality of all type of products. These computer integration systems included a lot of components from very different technologies as hydraulic, pneumatic, electrical, robotics, chemical, etc. For this reason these type of systems requires workers with specific skills to ensure that they are working properly.

The Rotary Table Workstation 2, "AE-PLC-MR2", has been designed by EDIBON to study the mounting, quality control and feeding system integrated in a rotatory table. The rotary tables are a common configuration used in the computer integrated manufacturing systems.

The "AE-PLC-MR2" workstation includes a set of practical exercises through which the student will understand how to control an automatic rotary table system with a mounting, quality control and feeding system, integrated in it.

GENERAL DESCRIPTION

The "AE-PLC-MR2" an automatic rotary table with a feeder, quality control and mounting system integrated in it. The "AE-PLC-MR2" has a vertical storage, the system provide pieces one by one to the rotary table, then, a quality control system check the material and the color of the piece. Finally, if the piece has the desired color and material, is mounted inside of another piece. If the piece has not the desired color or material is discarded by the rotary table.

- The "AE-PLC-MR2" workstation is designed as a modular system to facilitate the understanding of the unit. The main components are:
 - The PLC: is composed by an AE-PLCB (with HMI devices, analog and digital input/output, etc.) unit and all the extra modules needed to perform a correct working of the workstation.
 - The control panel: with start/stop button, emergency pushbutton, reset button, light indicators to show current state of the process, etc.
 The pneumatic circuit: contains the required solenoid valves, the pressure components, the filters and regulators to assure the appropriate working of the unit.
 - The workstation: is composed by real industrial components used by the rotary table systems such as reed sensors, presence sensors, DC motor, inductive sensors, rotary table with 8 positions, etc.

The "AE-PLC-MR2" is an independent workstation that can work alone and/or in conjunction with other workstation to make up a complete Flexible Manufacturing system*.

*The Flexible manufacturing systems product list is available at "Flexible Manufacturing Systems (FMS)" area of the general catalogue.



ISO 9001: Quality Management (for Design, Manufacturing, Commercialization and After-sales service)







Optional



AE-PLC-MR2/ICAI. Interactive Computer Aided Instruction Software System:

With no physical connection between unit and computer (PC), this complete software package consists of an Instructor Software (EDIBON Classroom Manager -ECM-SOF) totally integrated with the Student Software (EDIBON Student Labsoft -ESL-SOF). Both are interconnected so that the teacher knows at any moment what is the theoretical and practical knowledge of the students.

Instructor Software

- ECM-SOF. EDIBON Classroom Manager (Instructor Software).

ECM-SOF is the application that allows the Instructor to register students, manage and assign tasks for workgroups, create own content to carry out Practical Exercises, choose one of the evaluation methods to check the Student knowledge and monitor the progression related to the planned tasks for individual students, workgroups, units, etc... so the teacher can know in real time the level of understanding of any student in the classroom.

Innovative features:

- User Data Base Management.
- Administration and assignment of Workgroup, Task and Training sessions.
- Creation and Integration of Practical Exercises and Multimedia Resources.
- Custom Design of Evaluation Methods.
- Creation and assignment of Formulas & Equations.
- Equation System Solver Engine.
- Updatable Contents.
- Report generation, User Progression Monitoring and Statistics.



ETTE. EDIBON Training Test & Exam Program Package - Main Screen with Numeric Result Question



ECM-SOF. EDIBON Classroom Manager (Instructor Software) Application Main Screen



ECAL. EDIBON Calculations Program Package - Formula Editor Screen



ERS. EDIBON Results & Statistics Program Package - Student Scores Histogram

Optional

Student Software

- ESL-SOF. EDIBON Student Labsoft (Student Software).

ESL-SOF is the application addressed to the Students that helps them to understand theoretical concepts by means of practical exercises and to prove their knowledge and progression by performing tests and calculations in addition to Multimedia Resources. Default planned tasks and an Open workgroup are provided by EDIBON to allow the students start working from the first session. Reports and statistics are available to know their progression at any time, as well as explanations for every exercise to reinforce the theoretically acquired technical knowledge.

Innovative features:

- Student Log-In & Self-Registration.
- Existing Tasks checking & Monitoring.
- Default contents & scheduled tasks available to be used from the first session.
- Practical Exercises accomplishment by following the Manual provided by EDIBON.
- Evaluation Methods to prove your knowledge and progression.
- Test self-correction.
- Calculations computing and plotting.
- Equation System Solver Engine.
- User Monitoring Learning & Printable Reports.
- Multimedia-Supported auxiliary resources.

For more information see ICAI catalogue. Click on the following link: www.edibon.com/en/files/expansion/ICAI/catalog



ERS. EDIBON Results & Statistics Program Package - Question Explanation



ESL-SOF. EDIBON Student LabSoft (Student Software) Application Main Screen



EPE. EDIBON Practical Exercise Program Package Main Screen

	SMEAD	SHET	
	Plot Table Plot Function	Save Table	Open Help (F1) Call
	$Aout = \left(\frac{lvalue}{2^{Nbits}}\right) \times 10$		
When		contrology point 1 (33/kg)	
irge Picture			- I
Entropy (1) (1) (1)	Contradign (p. J Aug	Lethings) (subig	1091
irge Picture	Contractory of Sciences Sciences		
arge Picture	Consept pulsa St		000
arge Picture	timingstation St		000
arge Picture	tensional backage 50		000
arge Picture	Conhoigent (BLIAU) 20		000
arge Picture	Centraliyy10x35xp 30		000
arge Picture	Kolokyy a Ango Sy		000
arge Picture	Gology (6,24g) 39		000
arge Picture	Entropy (LAng 30		000
arge Picture	Gobayyi Qung 39		000
arge Picture	Lelayt (JA)		000

ECAL. EDIBON Calculations Program Package Main Screen

* Specifications subject to change without previous notice, due to the convenience of improvement of the product.



C/ Del Agua, 14. Polígono Industrial San José de Valderas. 28918 LEGANÉS. (Madrid). ESPAÑA - SPAIN. Tel.: 34-91-6199363 Fax: 34-91-6198647 E-mail: edibon@edibon.com Web: **www.edibon.com**

Edition: ED02/17 Date: July/2017 **REPRESENTATIVE:**